



Service Entrance Splices

T&B Catalog Number:

KL56-1

UPC Number:

78378605007

Status:

Active

Description:

Aluminum 3 1/2" Service Entrance Compression Splice for Wire Range - End A: 3/0 ASCR, 4/0 Str. Compact, Yellow, End B: 1/0 ASCR, 1/0 Str., 2/0 Str. Compact, Yellow, Die: 840

Features

Use for combinations of aluminum-to-aluminum and aluminum-to-copper conductors. Can be used as a low-cost reducing sleeve.

Center stop to ensure proper conductor positioning. Color-coded and marked for easy identification.

Standards compliant. Meets ANSI C119.4 requirements.

General

Insulation Type	Non-Insulated
Material	Aluminum
Barrel Length	Longer Length
Conductor Range A ASCR	3/0
Conductor Range A Str./Sol.	4/0 Str. Compact
Conductor Range B ASCR	1/0
Conductor Range B Str./Sol.	1/0 Str., 2/0 Str. Compact
Conductor A Color	Black
Conductor B Color	Yellow

Dimension Information

Length (inches)	3.5
Conductor A Diameter Max.	0.502
Conductor A Diameter Min.	0.464
Conductor B Diameter Max.	0.398
Conductor B Diameter Min.	0.368

Tooling

Die Series	840 Die Series
Hydraulic Dies	840, U-K840 U-249, B49EA
Mechanical Dies	840, W-K840 EEI-11A, TX

Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	17.56 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com