



Split-Bolt T&B Catalog Number:

UPC Number:

500HPS

Status:

78378685525

Description:

Active

Type HPS Plated Split-Bolt Connector with Spacer made of Copper Alloy for Use on Copper, Aluminum, ACSR Conductors. Conductor Range for Equal Main and Tap 500 kcmil-1/0 Str.

Features

Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of bronze alloy copper.

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style	Type HPS
Wire Type	Copper, Aluminum, ACSR
Material	Copper Alloy
Plating	Electro Tin-Plated
Color	Metallic
Conductor Range for Equal Main and Tap 500 kcmil-1/0 Str.	
Conductor Range Min. Tap with one Max. 1/0 Str.	
Main	
Conductor Range For Equal Main and Tap ACSR	397.5-1/0

Dimension Information

A (inches)	1 1/2
B (inches)	0.842
C (inches)	1 7/8
D (inches)	3 1/32

Packaging

T&B Inner Pack	1
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	109.38 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000072
--------------------	------------

Notes

Most connectors are UL and CSA Certified for copper conductor only.

Blackburn Contax recommended when used on aluminum conductor.

Not CSA Certified.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com