

**Ground Clamps**
T&B Catalog Number:**UPC Number:****Status:****Description:**

JDLI

78378643783

Active

Direct Burial Ground Clamp for Wire Range 10 - 2, Pipe Size 1/2 - 1,
Ground Rod Range 1/4 - 1**Features**

Lay-in feature reduces installation time for difficult bends or continuous loops of ground wire. UL listed for connection to ground rod, pipe or rebar up to 1 inch.

Constructed from bronze alloy and high performance stainless steel bolts.

General

Style	Direct Burial
Material	Bronze Alloy
Wire Range	10 - 2

Dimension Information

IPS Pipe Size (inches)	1/2 - 1
Rebar Size (inches)	3/8 - 1

Packaging

T&B Order Multiple	25
T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	23.31 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000075
--------------------	------------

Notes

UL Listed for direct burial in earth/concrete
Mechanical conn./splice (2) 8 Solid

Certifications

RoHS Compliance	Yes
-----------------	-----

CertificationsFile Nbr:
467**For further technical assistance, please contact us...**

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com