



## Dual-Rated T&B Catalog Number:

ASL60-32  
78378613316  
Active

## UPC Number: Status: Description:

Type ASL-ALCUL Three-Conductor, Two-Hole Mount for Conductor  
Range Max 600 kcmil, Min 2 Str.

## Features

Easy Installation - no special tools required.

## General

Style	ALCUL Three-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	600 kcmil
Conductor Range (AL or CU) Minimum	2 Str.

## Dimension Information

Length (inches)	4 29/32
Width (inches)	2 1/2
Height (inches)	3
D (inches)	3/8
F (inches)	3/4
I (inches)	1 7/32

## Packaging

T&B Order Multiple	3
T&B Inner Pack	3
Package in Units	18
T&B Sold in UOM	Each
T&B Weight Per UOM	1.29 lbs. Each

## Application Support

T&B Sales Drawings	wsd-000463
--------------------	------------

## Notes

UL 486B tested, AL9CU rated

## Certifications

RoHS Compliance	No
-----------------	----

## Certifications



File Nbr:  
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com