

IKL58



## **Blackburn®**

Type IKL - Insulated service entrance sleeve, 840 die. End "A" conductor range diameter 0.502 - 0.464. End "B" conductor range diameter 0.502 - 0.464.

### General

Type:	Service Entrance Splices
Application:	Ideal for heavy-duty overhead services
T&B UPC:	78378605032
T&B Status:	M
Special Features:	Provides high-conductivity
Material:	Aluminum

### Dimension Information

Conductor A / ACSR:	ACSR 3/0
Conductor A / Colour:	Black
Conductor A / Compact:	4/0 AWG
Conductor A / Compressed:	3/0 AWG
Conductor A / Stranded:	3/0 str.
Conductor B / ACSR:	ACSR 3/0
Conductor B / Colour:	Black
Conductor B / Compact:	4/0 AWG
Conductor B / Compressed:	3/0 AWG
Conductor B / Stranded:	3/0 str.