



Split-Bolt
T&B Catalog Number:

10H
 78378620014
 Active

UPC Number:
Status:
Description:

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 1/0 Str.-4 Sol.

Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

Standards

UL, CSA

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style Type H
 Wire Type Copper
 Material Bronze Alloy
 Color Metallic
 Conductor Range for Equal Main and Tap 1/0 Str.-4 Sol.
 Conductor Range Min. Tap with one Max. 14 Sol.
 Main

Dimension Information

A (inches) 3/4
 B (inches) 0.385
 C (inches) 15/16
 D (inches) 1 19/32

Packaging

T&B Inner Pack 50
 Package in Units 300
 T&B Sold in UOM Each
 T&B Weight Per UOM 16.62 lbs. per 100

Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
 E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com