



## Ground Rod Clamps T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

JAB34C  
78378613671  
Active

Ground Rod Clamps Type JAB, Rod Size 3/4 + 5/8, Wire Range 8 Sol. - 3/0 Str.

### Features

Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.

Both hex head bolts and socket set screws available.

### General

Style	Type JAB
Material	Copper
Wire Range	8 Sol. - 3/0 Str.
Thread Size	7/16 - 14 UNC-2A
Ground Rod	3/4 + 5/8

### Dimension Information

Bolt Size (inches)	2 11/32
B (inches)	1 1/16
C (inches)	1
D (inches)	51/64

### Packaging

T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	18.75 lbs. per 100

### Application Support

T&B Sales Drawings	wsd-000478
Overview	Available on Website

### Notes

Add suffix P to Catalog number for tin-plated clamp.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com