



## Split-Bolt

**T&B Catalog Number:**

4H

**UPC Number:**

78378620025

**Status:**

Active

**Description:**

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 4 Sol.-8 Sol.

### Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

### Standards

UL, CSA

### Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

### General

Style	Type H
Wire Type	Copper
Material	Bronze Alloy
Color	Metallic
Conductor Range for Equal Main and Tap 4 Sol.-8 Sol.	
Conductor Range Min. Tap with one Max. 14 Sol.	
Main	

### Dimension Information

A (inches)	17/32
B (inches)	0.235
C (inches)	23/32
D (inches)	1 1/16

### Packaging

T&B Inner Pack	100
Package in Units	600
T&B Sold in UOM	Each
T&B Weight Per UOM	7.06 lbs. per 100

### Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)