



**Split-Bolt**  
**T&B Catalog Number:**

30H  
 78378620016  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 4/0 Str.-2 Sol.

**Features**

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

**Standards**

UL, CSA

**Application**

Splicing, tapping or terminating conductors in power and grounding electrical connection.

**General**

Style	Type H
Wire Type	Copper
Material	Bronze Alloy
Color	Metallic
Conductor Range for Equal Main and Tap 4/0 Str.-2 Sol.	
Conductor Range Min. Tap with one Max. 6 Sol.	
Main	

**Dimension Information**

A (inches)	1
B (inches)	0.580
C (inches)	1 5/16
D (inches)	2 5/32

**Packaging**

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	35.94 lbs. per 100

**Notes**

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
 E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)