

## Splice Connector T&B Catalog Number:

RDD27

UPC Number:

78621089449

Status:

Active

Description:

Insulated Nylon Butt Splice Connector For Wire Range 8 Length 1.69 Diameter .36, Red

### WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.

### General

Insulation Type	Insulated Nylon
Terminal Series	RDD
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Wire Range	8

### Dimension Information

Maximum Insulation (inches)	.340
Stock Thickness	.04
A (inches)	1.69
B (inches)	.36

### Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

### Tooling

Tool Charts	Available on Website
Application Tools	TBM6, TBM6S, ERG4007
Recommended Tool	ERG4007, TBM6S

### Packaging


T&B Order Multiple	200
T&B Inner Pack	200
Package in Units	2000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	1.33 lbs. per 100
Alternate Package Qty	2RD8

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

### Certifications

RoHS Compliance	Yes
-----------------	-----



## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)