Thomas@Betts





18RA-10FX

UPC Number: 78621080094 **Status:** Active

Status: Description:


Expanded Insulated Vinyl Fork Terminal For Wire Range 22-16 Stud Size #10, Red




US Cutsheet PDF Catalog Link http://www-public.tnb.com/contractor/docs/

stakon.pdf

Features





General	
Insulation Type	Expanded Insulated Vinyl
Terminal Series	RA
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-16
Stud Size	#10
Dimension Information	
Maximum Insulation (inches)	.170
Stock Thickness	.03
A (inches)	.97
B (inches)	.31
C (inches)	.27
M (inches)	.81
Specifications	
Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0
Tooling	
Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001
Packaging	
T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.25 lbs. per 100
Alternate Package Qty	RA1157-170
Application Support	
Overview	Available on Website



Wire Guide Tables Available on Website

Certifications

RoHS Compliance Yes

Certifications





File Nbr: E9809

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com