



Locking Fork Terminal T&B Catalog Number:

UPC Number:
Status:
Description:

RB14-6FL
78621088739
Active

Insulated Nylon Locking Fork Terminal For Wire Range 18-14 Stud Size #6, Blue


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.



General

Insulation Type	Insulated Nylon
Terminal Series	RB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	18-14
Stud Size	#6

Dimension Information

Maximum Insulation (inches)	.162
Stock Thickness	.03
A (inches)	.87
B (inches)	.25
C (inches)	.25
M (inches)	.71

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	ERG4001, ERG4003, WT145C, WT2000, WT112M, WT145A
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.26 lbs. per 100
Alternate Package Qty	RB2213

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com