



Disconnects
T&B Catalog Number:

RA18-110F

UPC Number:

78621080682

Status:

Active

Description:

Insulated Nylon Female - 110 Series Disconnects For Wire Range 22-18 Length 0.75, Red

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

General

Disconnect Type	Female - 110 Series
Insulation Type	Insulated Nylon
Terminal Series	RA
Material	Brass
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-18
Tab Size	.110 x .032

Dimension Information

Maximum Insulation (inches)	.110
Stock Thickness	.03
A (inches)	.75
B (inches)	.15

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Recommended Tool	ERG4006

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.15 lbs. per 100
Alternate Package Qty	RA10SK

Application Support

Wire Guide Tables	Available on Website
-------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

