

°HAND DRYER

SHDL SERIES

SAME MODEL, TWO VERSIONS

The SHDL series hand dryer is constructed with a one-piece, ultra-resistant Lexan cover and is surface-mounted onto the wall. It is available either fully automatic or with a push button.

- **STARTS AND STOPS AUTOMATICALLY**
(SHDLAS MODEL)
- **PUSH BUTTON**
STARTS AND STOPS MANUALLY (SHDLPB MODEL)



FEATURES

COLOR

white

MANUFACTURING

- shell is a one-piece mold of Lexan 940
- secured to a zinc alloy wall bracket with two chrome-plated, tamper-proof bolts
- chrome-plated, die-cast zinc turbine forces air
- tamper-proof vent, preventing the insertion of foreign objects

SOUND LEVEL

72 dBA

ELEMENT

nichrome

CONTROL

- SHDLAS model - an infrared optical sensor located next to the air outlet activates the hand dryer
- a 90-second lockout feature is activated if hands are not removed before this time
- SHDLPB model - push button start
- built-in 30-second sealed electronic timer

INSTALLATION

wall mounted

TECHNICAL SPECIFICATIONS

PRODUCT	POWER	VOLTAGE	AMPERAGE	WEIGHT	
CODE	WATTS	VOLTS	AMPERES	KG	LB
SHDLAS1W	2000	120	20	9.0	20
SHDLAS8W	2000	208	11	9.0	20
SHDLAS2W	2000	240	10	9.0	20
SHDLPB1W	2000	120	20	8.1	18
SHDLPB8W	2000	208	11	8.1	18
SHDLPB2W	2000	240	10	8.1	18

* FOR US ORDERS: please add the letter "A" in front of the product code

RECOMMENDED INSTALLATION HEIGHTS

Distance between floor and bottom of hand dryer

MEN	WOMEN	TEENAGERS	CHILDREN	HANDICAPPED
43" (109 cm)	41" (104 cm)	39" (99 cm)	33" (84 cm)	35" (89 cm)

TECHNICAL DRAWINGS

