



## Splice Connector T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

2RBB  
78621080021  
Active

Insulated Nylon Aircraft Splice Connector For Wire Range 16-14 Length 1.52 Diameter .28, Blue

### WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.



### General

Insulation Type	Insulated Nylon
Terminal Series	RBB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14

### Dimension Information

Stock Thickness	.03
A (inches)	1.52
B (inches)	.28

### Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

### Tooling

Tool Charts	Available on Website
Application Tools	WT145C, ERG4001, ERG4003
Recommended Tool	ERG4001

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	6.25 lbs. per 1000
Alternate Package Qty	RBB23

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)