



Splice Connector
T&B Catalog Number:

54507

UPC Number:

78621054507

Status:

Active

Description:

Copper Two-Way Splice - Short Barrel for 2 AWG, 125/24, 4 Weld, Die Code 33 Brown

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#2 AWG
Wire Size Flex	125/24 = 50.4 kcmil, #4 Weld
Die Color	Brown
Die Code	33

Dimension Information

A (inches)	1.25
E (inches)	.41

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	2.74 lbs. per 100

Application Support

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com