



Automatic Splices T&B Catalog Number:

ATS3040
78378610382
Active

UPC Number:
Status:
Description:

Autoset Automatic Tension Splice for Wire Range: 3/0 6/1, 4/0 6/1 ASCR, 3/0-4/0 AAAC, 3/0-4/0 AAC, Aluminum, Color Code 3/0 - Black, 4/0 - Pink

Features

Color-coded end pieces provide for visual identification of maximum conductor size. Color-coded tape further eliminates errors and speeds up installations. Funnel shape swiftly guides conductor into position for insertion.

Pilot cap envelops strands and guides conductor past serrated jaws and into the center of the splice.

Die-cast, precision-made jaws provides optimum contact area for a greater range of conductor sizes. Compression spring positions the jaw for positive conductor acceptance.

High-Strength aluminum alloy tubing covers the connection for superior corrosion protection and long-lasting durability. Tubular center stop automatically determines proper insertion length of both conductors.

General

Style	ATS Autoset
Material	Aluminum
Conductor Range - ASCR	3/0 6/1, 4/0 6/1
Conductor Range AAAC	3/0-4/0
Conductor Range AAC	3/0-4/0
Color Code	3/0 - Black, 4/0 - Pink

Dimension Information

Length (inches)	23 1/2
-----------------	--------

Packaging

T&B Order Multiple	10
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	183.5 lbs. per 100

Application Support

T&B Instruction Sheets	027-365-02-tb2
------------------------	----------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com