



Disconnects T&B Catalog Number:

14RBD-18377

UPC Number: 78621081867 Status: Active

Description:

Fully Insulated Nylon Female - 187 Series Disconnects For Wire Range 16-14 Length 0.89, Tab Size .187 x .032 , Blue

16-14 Length 0.89, Tab Size .187 x .032 , Blue	
WEB_USE	
US Cutsheet PDF Catalog Link	http://www-public.tnb.com/contractor/docs/ stakon.pdf
Features	
	Quick, reliable method of connection to terminal
	blocks and boards without the use of tools. Unique
	construction of the female disconnect offers long-
	term dependability.
General	
Discoursed Time	Formale 407 Carina
Disconnect Type	Female - 187 Series
Insulation Type Terminal Series	Fully Insulated Nylon RBD
Material Finish	Brass Electro -Tin Plated
Color Wire Range	Blue 16-14
Tab Size	.187 x .032
Dimension Information	.107 X .032
Maximum Insulation (inches)	.170
Stock Thickness	.03
A (inches)	.89
B (inches)	.30
Specifications	
Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2
Tooling	
To all Oh auto	Accellate and Waterie
Tool Charts	Available on Website
Application Tools Recommended Tool	WT145C, WT2000, WT112M, ERG4001, ERG4003 ERG4002
Packaging	ERG4002
rackaging	
T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	3.75 lbs. per 1000
Alternate Package Qty	RBD18377
Application Support	
Overview	Available on Website
Wire Guide Tables	Available on Website



Certifications

RoHS Compliance

Yes

Certifications





File Nbr: E66716

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321

Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com