

ELECTRONIC THERMOSTAT

STE302P-STE402P SERIES

M MULTIPLE PROGRAMMING


3000 W

4000 W

THE SMART, EFFICIENT AND ECOLOGICAL CHOICE

Cost-saving programming, that's what this thermostat has to offer. Life just got both simpler and more comfortable thanks to its Preprogrammed mode that allows you to easily and quickly program the desired temperature. Offering 18 predefined programs, the user can easily select among the most commonly used settings or program their own custom settings.



- 18** **EASY PROGRAMMING**
INCLUDES 18 PREPROGRAMMED PRESETS IN "PRE-PROG" MODE
- ± 0.1°F** **INCREASED SAVINGS AND COMFORT**
INCOMPARABLE ACCURACY
-  **ANTICIPATED START**
REACH THE SELECTED TEMPERATURE AT PRECISELY THE PROGRAMMED TIME
- 5-2** **5-2 DAY PROGRAMMING**
-  **BACKLIT SCREEN**
MAY BE USED AS A NIGHTLIGHT

MORE THAN 30% **CONSUMPTION SAVINGS**
ENERGY SAVINGS OF MORE THAN 30% WITH DAY/NIGHT TEMPERATURE REDUCTION OF 8 °F

COLOR

white

FINISH

molded plastic

WATTAGE & VOLTAGE

STE302P: 150 W to 1500 W @ 120 V / 260 W to 2600 W @ 208 V / 300 W to 3000 W @ 240 V

STE402P: 150 W to 2000 W @ 120 V / 260 W to 3475 W @ 208 V / 300 W to 4000 W @ 240 V

CONTROL

- 2-wire connection
- compatible with forced-air units (Fan mode)
- easily choose the desired preprogramming with one button
- able to program 4 periods a day during the week and 4 others per day during the weekend, for a maximum of 8/week
- anticipated start (the thermostat reaches the desired temperature at the requested hour)
- frost-free warning
- lock option at a minimum and maximum temperature set point (Security mode)
- protection against power failure (2 hours)
- the hour can be displayed in 12 or 24-hour mode
- display in either Fahrenheit or Celsius

ACCURACY

accurate ambient temperature control of ± 0.18 °F

TEMPERATURE RANGE

between 37 to 86 °F

DESIGNED FOR



AND MORE...

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	PACKAGING
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ	
STE302PWB+	150/260/300	1500/2600/3000	120/208/240	12.5	50/60	BOX
STE402PWB+	150/260/300	2000/3475/4000	120/208/240	16.7	50/60	BOX

DIMENSIONS: width of 4 7/8 in., height of 4 7/8 in. and depth of 1 1/8 in.



*STELPRO reserves the right to modify descriptions or manufacturing specifications without prior notice. For all the latest models and prices, please refer to our website at www.stelpro.com.