



Splice Connector
T&B Catalog Number:

54011
 78621054011
 Active

UPC Number:
Status:
Description:

Copper Two-Way Splice - Long Barrel for 3/0 AWG, Die Set 15CA49R Orange

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	3/0 AWG
Strip Length (inches)	1 13#16
Die Color	Orange
Die Set	15CA49R



Dimension Information

Strip Length (inches)	1 13#16
A (inches)	2.63
E (inches)	0.63

Specifications

Voltage Rating	600V
----------------	------

Tooling

Application Tools	13100A, TBM15I, TBM14M
-------------------	------------------------

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	6.88 lbs. per 100

Notes

Cat. No. 15500-TB Die Adapter required for TBM15I Tool.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
 Y

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

