



## Splice Connector T&B Catalog Number:

**UPC Number:**

**Status:**

**Description:**

54506

78621054506

Active

Copper Two-Way Splice - Short Barrel for 4 AWG, 91/24 Die Code 29  
Gray

### Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

### General

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#4 AWG
Wire Size Flex	91/24 = 36.7 kcmil, 133/.0177, 49/.029
Die Color	Gray
Die Code	29

### Dimension Information

A (inches)	1.00
E (inches)	.37

### Specifications

Voltage Rating	600V
----------------	------

### Packaging

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	1.72 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com