

PB324

Pos-E-Kon™

Single lever locking panel base



General

Type:	10 A, 16 A 600 VAC
T&B UPC:	78621083661
T&B Status:	M
Series:	B series
Housing:	Panel base without cover
Flammability:	UL94 V-0
Approvals:	MEIE, EZU, SEV
Housing Series:	B24, K12, D64 and DD108
Housing Temperature Range:	-40°C/-40°F to +125°C /+257°F
Insert Material:	Glass-filled thermoplastic
Insert Temperature Range:	-40°C/-40°F to +125°C /+257°F
Lever Locking Type:	Single
Screw Terminal:	20-14 AWG
Test Voltage:	3 kV eff.
Working Current:	16 A max.
Special Features:	IP65 locked positions per DIN VDE 0470, IEC 529
Voltage Rating:	600 VAC
Material:	Die-cast aluminum alloy

Dimension Information

Contact Material:	Solid drilled copper alloy
Contact Resistance:	# 1milliohm
Contact Surface:	Hard silver plated, Hard gold plated
Contact Type:	24 contacts with ground connection
Crimp Terminal:	20-12 AWG
EPDM Seal Gaskets:	Epoxy powder-coat finish