



Service Entrance Fittings

T&B Catalog Number:

2446

UPC Number:

78621002446

Status:

Active

Description:

1 1/4" Watertight Connector for Oval Cable, Die Cast Zinc. Oval cable range-Maximum-.750 x 1.150; Minimum-.565 x .965.

Features

A design with two tapers inside the body-a slow one and a fast one-permits the stocking of fewer connectors for varied cable sizes and allows maximum take-up.

The tapered neoprene bushings are resistant to oil, sunlight and water. Hex gland and body take the same wrench opening and a stainless steel slip ring prevents cable from twisting as gland ring is being tightened. Threads on the body are tapered for watersealing.

Application

To connect underground feeder cables to a box or an enclosure.

General

Material Die Cast Zinc

Dimension Information

| | |
|-----------------------------------|------------|
| Hub Size (inches) | 1 1/4 |
| Oval Cable Range-Maximum (inches) | .750x1.150 |
| Oval Cable Range-Minimum (inches) | .565x.965 |

Specifications

3dmodel Available on Website

Packaging

| | |
|--------------------|-----------------|
| T&B Inner Pack | 5 |
| Package in Units | 50 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 56 lbs. per 100 |

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E 15170

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com