



Disconnects

T&B Catalog Number:

UPC Number:
Status:
Description:

C10-250F
78621080352
Active

Non-Insulated Female - 250 Series Disconnects For Wire Range 12-10
Length 0.73, Tab Size .250 x .032 , Metallic

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

General

| | |
|-----------------|---------------------|
| Disconnect Type | Female - 250 Series |
| Insulation Type | Non-Insulated |
| Terminal Series | C |
| Material | Brass |
| Finish | Electro -Tin Plated |
| Color | Metallic |
| Wire Range | 12-10 |
| Tab Size | .250 x .032 |

Dimension Information

| | |
|-----------------|-----|
| Stock Thickness | .04 |
| A (inches) | .73 |
| B (inches) | .31 |

Specifications

| | |
|---------------------|-----------|
| Temperature Rating | 150°C |
| Voltage Rating | 600V |
| Flammability Rating | UL 94 V-0 |

Tooling

| | |
|-------------------|---|
| Tool Charts | Available on Website |
| Application Tools | WT110M, WT111M, WT112M, WT2000, ERG4002 |
| Recommended Tool | ERG4002 |

Packaging

| | |
|-----------------------|--------------------|
| T&B Order Multiple | 50 |
| T&B Inner Pack | 50 |
| Package in Units | 250 |
| Package Type | Standard |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 4.38 lbs. per 1000 |
| Alternate Package Qty | C250 |

Application Support

| | |
|-------------------|----------------------|
| Overview | Available on Website |
| Wire Guide Tables | Available on Website |

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com