



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

276

UPC Number:

78621000276

Status:

Active

Description:

2 in. Malleable Iron Squeeze Connector-90 degree.

Features

Cap lifts off by simply loosening screws part way, only two screws to tighten.

Application

For use with Armored Cable and Flexible Metal Conduit.

General

Trade Size (inches)	2
Material	Malleable Iron
Finish	Zinc Plate

Dimension Information

Dimension A (inches)	4 1/2
Dimension B (inches)	3 13/16
Dimension C (inches)	4 7/8
Knockout Size (inches)	2
Cable Opening-Minimum (inches)	2.125
Cable Opening-Maximum (inches)	2.500

Packaging

T&B Inner Pack	1
Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	207 lbs. per 100

Notes

UL Listed for flexible metal conduit only.

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com