

Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

2564

UPC Number: 78621002564

Status: Active

Description:

1-1/2 in. straight die cast zinc liquidtight strain relief cord connector, cord range-1.187-1.375.

range-1.187-1.375.	
Application	
	Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).
	Meets Coast Guard CG293
General	
Material	Die Cast Zinc
Dimension Information	
Hub Size (inches)	1 1/2
Dimension A (inches)	2 11/32
Dimension B (inches)	2 7/16
Dimension C (inches)	11/16
Cord Range (inches)	1.187-1.375
Throat Diameter (inches)	1 7/16
Specifications	
3dmodel	Available on Website
Temperature Rating	105 C
Packaging	
T&B Inner Pack	5
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	82 lbs. per 100
Application Support	
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website
Notes	
	Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).
Certifications	
RoHS Compliance	Yes
Certifications	



File Nbr:

E 13938

For further technical assistance, please contact us...



8155 T&B Blvd. Memphis, TN 38125 www.tnb.com MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com