



Fork Terminal T&B Catalog Number:

UPC Number:
Status:
Description:

C10-8F
78621080345
Active

Non-Insulated Fork Terminal For Wire Range 12-10 Stud Size #8, Metallic
WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

These non-insulated fork terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.

General

Insulation Type	Non-Insulated
Terminal Series	C
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	12-10
Stud Size	#8

Dimension Information

Stock Thickness	.04
A (inches)	.82
B (inches)	.38
C (inches)	.27
M (inches)	.63

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT110M, WT111M, WT112M, WT2000, ERG4002
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	5 lbs. per 1000
Alternate Package Qty	C114

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com