



## Splice Connector T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

54010  
78621054010  
Active

Copper Two-Way Splice - Long Barrel for 2/0 AWG, Die Set 15CA45R  
Black

### Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

### General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	2/0 AWG
Strip Length (inches)	1 3/4
Die Color	Black
Die Set	15CA45R

### Dimension Information

Strip Length (inches)	1 3/4
A (inches)	2.38
E (inches)	0.57

### Specifications

Voltage Rating	600V
----------------	------

### Tooling

Application Tools	13100A, TBM15I, TBM14M
-------------------	------------------------

### Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	8.19 lbs. per 100

### Notes

Cat. No. 15500-TB Die Adapter required for TBM15I Tool.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289

