



Liquidtight Flexible Metal Conduit Fittings

T&B Catalog Number:

5347

UPC Number:

78621005347

Status:

Active

Description:

2 Inch 45 degree malleable iron insulated liquidtight connector

Features

Ability to install quickly with low torque effort

Application

Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.

To positively bond conduit to box or enclosure.

General

Style	Insulated
Trade Size (inches)	2
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

Dimension Information

Dimension A (inches)	3 1/4
Dimension B (inches)	3 7/8
Dimension C (inches)	7/8

Specifications

3dmodel	Available on Website
---------	----------------------

Accessories & Components

Wiremesh Grips for Liquidtight Fittings	WMG-LT7
-----------------------------------------	---------

Packaging

T&B Inner Pack	1
Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	213 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com