



Ring Terminal T&B Catalog Number:

UPC Number:

B14-4

Status:

78621080314

Description:

Active

Non-Insulated Ring Terminal For Wire Range 18-14 Stud Size #4, Metallic
WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.

General

Insulation Type	Non-Insulated
Terminal Series	B
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	18-14
Stud Size	#4

Dimension Information

Stock Thickness	.03
A (inches)	.72
B (inches)	.25
C (inches)	.27
M (inches)	.59

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT110M, WT111M, WT112M, WT2000, ERG4002
Recommended Tool	ERG4002, ERG4005

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 1000
Alternate Package Qty	B132

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com