



## Disconnects

**T&B Catalog Number:**

RBD1837

**UPC Number:**

78621081739

**Status:**

Active

**Description:**

Insulated Vinyl Female - 187 Series Disconnects For Wire Range 16-14 Length 0.85, Tab Size .187 x .032 , Blue

### WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.

### General

Disconnect Type	Female - 187 Series
Insulation Type	Insulated Vinyl
Terminal Series	RBD
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14
Tab Size	.187 x .032

### Dimension Information

Maximum Insulation (inches)	.170
Stock Thickness	.03
A (inches)	.85
B (inches)	.23

### Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

### Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

### Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.33 lbs. per 100
Alternate Package Qty	14RBD183

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

## Notes

Bulk catalog numbers can be put on Mylar Tape for reel-fed applications (i.e. 12050 tool and application dies). Please add the suffix M for Mylar tape.

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E66716

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com