



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

310

UPC Number:

78621000310

Status:

Active

Description:

1 1/2 in. Tite-Bite Connector, Malleable Iron-Electro Zinc Plated

Features

Easy to install with double grip saddle, connectors are completely salvageable.

Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

General

Trade Size (inches)

1 1/2

Material

Malleable Iron

Finish

Electro Zinc Plated

Dimension Information

Dimension A (inches)

2 5/8

Dimension B (inches)

2 9/16

Dimension C (inches)

1 3/4

Knockout Size (inches)

1 1/2

Cable Opening-Minimum (inches)

1.812

Cable Opening-Maximum (inches)

2.031

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

5

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

118 lbs. per 100

Notes

UL Listed for flexible metal conduit only.

Certifications

RoHS Compliance

No

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com