



**Liquidtight Flexible Cord & Cable Fittings**

**T&B Catalog Number:**

2541

**UPC Number:**

78621002541

**Status:**

Active

**Description:**

1 in. straight die cast zinc liquidtight strain relief cord connector, cord range-.250-.375.

**Application**

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

**General**

Material Die Cast Zinc

**Dimension Information**

Hub Size (inches)	1
Dimension A (inches)	1 3/8
Dimension B (inches)	1 23/32
Dimension C (inches)	9/16
Cord Range (inches)	.250-.375
Throat Diameter (inches)	49/64

**Specifications**

3dmodel	Available on Website
Temperature Rating	105 C

**Packaging**

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	25.38 lbs. per 100

**Application Support**

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

**Notes**

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

**Certifications**

RoHS Compliance Yes

**Certifications**



File Nbr:  
E 13938

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)