

**Rigid/IMC Conduit Fittings****T&B Catalog Number:**

3212

UPC Number:

78621003212

Status:

Active

Description:

One piece non-metallic knockout bushing, thermoplastic, knockout size 1.375. For use with Rigid/IMC Conduit.

Application

To bush knockout openings in metal boxes or enclosures.

General

Material	Polycarbonate
Color	Black

Dimension Information

Dimension B (inches)	0.36
Knockout Size (inches)	1.375

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	8.75 lbs. per 1000

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com