



## Ring Terminal T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

RA18-6  
78621080385  
Active

Insulated Nylon Ring Terminal For Wire Range 22-16 Stud Size #6, Red  
**WEB\_USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

Self-insulated with high dielectric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.

### General

Insulation Type	Insulated Nylon
Terminal Series	RA
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-16
Stud Size	#6

### Dimension Information

Maximum Insulation (inches)	.136
Stock Thickness	.03
A (inches)	.86
B (inches)	.26
C (inches)	.25
M (inches)	.74

### Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

### Tooling

Tool Charts	Available on Website
Application Tools	WT2000, WT112M, WT145C, ERG4001, ERG4003, WT145A
Recommended Tool	ERG4001

### Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.24 lbs. per 100
Alternate Package Qty	RA333

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)