

10603



T&B Industrial Fitting

90 degrees watertight fittings made of malleable iron with a protective grounding sleeve for jacketed metal-clad cable. Hub thread size 1/2 in.

General

T&B Instruction Sheets:	TA00316-TB2
Type:	90 degrees Watertight Fittings and Non-Watertight Teck Cable Fittings
Application:	Ordinary wet location
T&B UPC:	78621010603
T&B Status:	M
Hub Size:	1/2 in.
Material:	Malleable iron

Dimension Information

Neoprene Bushing Max.:	0.985 in.
Neoprene Bushing Min.:	0.875 in.