



Dual-Rated
T&B Catalog Number:

ADR35
78378661019
Active

UPC Number:
Status:
Description:

Type ADR-ALCUL Single-Conductor, One-Hole Mount for Conductor Range Max 350 kcmil, Min 6 Str.

Features

Easy Installation - no special tools required.

General

Style	ALCUL Single-Conductor, One-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	350 kcmil
Conductor Range (AL or CU) Minimum	6 Str.

Dimension Information

Length (inches)	2 1/4
Width (inches)	1 1/8
Height (inches)	1 1/4
D (inches)	1/2
E (inches)	3/8
F (inches)	1/4
G (inches)	1 1/8

Packaging

T&B Inner Pack	12
Package in Units	120
T&B Sold in UOM	Each
T&B Weight Per UOM	15.31 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000391
--------------------	------------

Notes

5/16 Socket screw on sizes 250 through 350 kcmil.
UL 486B tested, AL9CU rated

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com