



**Disconnects**  
**T&B Catalog Number:**

RC10-250A

**UPC Number:**

78621089447

**Status:**

Active

**Description:**

Insulated Nylon Female - 250 Series Disconnects For Wire Range 12-10 Length 0.8, Tab Size .250 x .032 , Yellow

**WEB\_USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

**General**

Disconnect Type	Female - 250 Series
Insulation Type	Insulated Nylon
Terminal Series	RC
Material	Brass
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	12-10
Tab Size	.250 x .032

**Dimension Information**

Maximum Insulation (inches)	.250
A (inches)	.80
B (inches)	.88

**Specifications**

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

**Tooling**

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.74 lbs. per 100
Alternate Package Qty	RC2577F

**Application Support**

Overview	Available on Website
Wire Guide Tables	Available on Website

**Certifications**

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E66716

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)