



## Disconnects

### T&B Catalog Number:

14RB-250FCP

### UPC Number:

78621089939

### Status:

Active

### Description:

Mini-Pack Insulated Vinyl Female - 250 Series Disconnects For Wire Range 16-14 Length 0.96, Tab Size .250 x .032 , Blue

### WEB\_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

### General

Disconnect Type	Female - 250 Series
Insulation Type	Insulated Vinyl
Terminal Series	RB
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14
Tab Size	.250 x .032

### Dimension Information

Maximum Insulation (inches)	.170
Stock Thickness	.03
A (inches)	.96
B (inches)	.29

### Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

### Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

### Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	100
Package Type	Mini-Pack
T&B Sold in UOM	Each
T&B Weight Per UOM	4.38 lbs. per 1000
Alternate Package Qty	14RB250F

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

### Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E66716

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)