



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2920NM

UPC Number:

78621079740

Status:

Active

Description:

1/2 in. straight nylon Ranger liquidtight cord connector, cord range .125-.375

Features

Extended range with superior strain relief.

Reduced overall size, fits into tighter spaces.

Gland nut designed to restrict cable bending.

Application

Provide a means for passing a cord cable into an enclosure through a bulkhead

Suitable for Ordinary, Wet or Dry locations.

General

Material Nylon

Cord and Cable Types S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

Dimension Information

Hub Size (inches) 1/2

Dimension A (inches) 1 7/32

Dimension B (inches) 2 1/8

Dimension C (inches) 5/8

Cord Range (inches) .125-.375

Throat Diameter (inches) 0.55

Specifications

3dmodel Available on Website

Packaging

T&B Inner Pack 25

Package in Units 100

T&B Sold in UOM Each

T&B Weight Per UOM 3.56 lbs. per 100

Application Support

T&B Instruction Sheets ta00927-tb2

Product Overview Available on Website

Specifications Available on Website

Portable Cord Selection Table Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E 13938

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com