



C-Tap
T&B Catalog Number:

54730

UPC Number:

78621054730

Status:

Active

Description:

Copper C-Tap for Wire Range Main: 4-2, Branch 4-12, Pink 42

Features

Positive, all-around compression with low resistance and high pull-out values.

Ideal for pigtailing, 2-way splicing or tapping to an unbroken continuous main.

Heavy reinforcing ribs help locate compression dies and strengthen compressed joint.

General

Style	Standard
Material	Copper
Finish	Plain
Wire Size	4-2
Die Color	Pink
Die Code	42

Dimension Information

H (inches)	27/32
L (inches)	1 5/32

Specifications

Voltage Rating	600V
----------------	------

Accessories & Components

Shrink Tubing	HS430
Hard Cover	HTC40

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	4.1 lbs. per 100

Application Support

T&B Instruction Sheets	ta00628-tb2
------------------------	-------------

Notes

Each C-Tap contains a range of conductor sizes. See Installation Instructions for wire range combinations.

UL approved for direct burial.

Taps can be supplied tin-plated. Add suffix TP to any catalog number.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
140B

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com