



Splice Connector
T&B Catalog Number:

2F-4
 78621080014
 Active

UPC Number:
Status:
Description:

Non-Insulated Butt Splice Connector For Wire Range 4-3 Length 1.25 Diameter .44, Metallic

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

General

Insulation Type	Non-Insulated
Terminal Series	F
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	4-3

Dimension Information

Stock Thickness	.07
A (inches)	1.25
B (inches)	.44

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT115A, TBM6, TBM6S
Recommended Tool	TBM6S

Packaging

T&B Order Multiple	15
T&B Inner Pack	15
Package in Units	150
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.06 lbs. per 100
Alternate Package Qty	FF2

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
 E9809



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com