



## Liquidtight Flexible Cord & Cable Fittings

**T&B Catalog Number:**

2562

**UPC Number:**

78621002562

**Status:**

Active

**Description:**

1-1/2 in. straight die cast zinc liquidtight strain relief cord connector, cord range-.812-1.000.

### Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

### General

Material Die Cast Zinc

### Dimension Information

Hub Size (inches)	1 1/2
Dimension A (inches)	2 11/32
Dimension B (inches)	2 1/2
Dimension C (inches)	11/16
Cord Range (inches)	.812-1.000
Throat Diameter (inches)	1 7/16

### Specifications

3dmodel	Available on Website
Temperature Rating	105 C

### Packaging

T&B Inner Pack	5
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	82 lbs. per 100

### Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

### Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E 13938

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)