

Technical Specifications



**CIRB6R4 /
CIRB16R12**



**BU-201 /
BU-210**



**CI2404 /
CI2448**



**CI2704 /
CI2748**

Rated 105°C



**CI2604 /
CI2632**

With solid copper lug.

Cat. No.	Trade Size	Cat. No.	Trade Size
Reducing Bushings - NPS (Steel)		Insulated Metallic Bushings (Aluminum)	
CIRB6R4	3/4 x 1/2	CI2404	1/2
CIRB8R4	1 x 1/2	CI2406	3/4
CIRB8R6	1 x 3/4	CI2408	1
CIRB10R4	1-1/4 x 1/2	CI2410	1-1/4
CIRB10R6	1-1/4 x 3/4	CI2412	1-1/2
CIRB10R8	1-1/4 x 1	CI2416	2
CIRB12R4	1-1/2 x 1/2	CI2420	2-1/2
CIRB12R6	1-1/2 x 3/4	CI2424	3
CIRB12R8	1-1/2 x 1	CI2428	3-1/2
CIRB12R10	1-1/2 x 1-1/4	CI2432	4
CIRB16R4	2 x 1/2	CI2440	5
CIRB16R6	2 x 3/4		
CIRB16R8	2 x 1		
CIRB16R10	2 x 1-1/4		
CIRB16R12	2 x 1-1/2		
Conduit Bushings (Zinc Die Cast)		Plastic Bushings	
BU-201	1/2	CI2704	1/2
BU-202	3/4	CI2706	3/4
BU-203	1	CI2708	1
BU-204	1-1/4	CI2710	1-1/4
BU-205	1-1/2	CI2712	1-1/2
BU-206	2	CI2716	2
BU-207	2-1/2	CI2720	2-1/2
BU-208	3	CI2724	3
BU-209	3-1/2	CI2728	3-1/2
BU-210	4	CI2732	4
		CI2740	5
		CI2748	6

Models CI2404 & CI2406 are in zinc.

Cat. No.	Trade Size	Ground Wire Size (AWG)
Insulated Grounding Bushings (Aluminum)		
CI2604	1/2	14-6
CI2606	3/4	14-6
CI2608	1	14-6
CI2610	1-1/4	14-4
CI2612	1-1/2	14-4
CI2616	2	6-1/0
CI2620	2-1/2	6-1/0
CI2624	3	2-4/0
CI2628	3-1/2	2-4/0
CI2632	4	2-4/0

