



Ring Terminal
T&B Catalog Number:

RBC14-10
78621089906
Active

UPC Number:
Status:
Description:


Insulated Nylon Ring Terminal For Wire Range 16-14 heavy duty Stud Size #10, Green

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.



General

Insulation Type	Insulated Nylon
Terminal Series	RBC
Material	Copper
Finish	Electro -Tin Plated
Color	Green
Wire Range	16-14 heavy duty
Stud Size	#10

Dimension Information

Maximum Insulation (inches)	.210
Stock Thickness	.03
A (inches)	1.04
B (inches)	.39
C (inches)	.29
M (inches)	.85

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	WT2000, ERG4001
Recommended Tool	WT2130A

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	6.88 lbs. per 1000
Alternate Package Qty	RBC873

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com