



Representative

Catalog Number: 58182
Product ID: 7TAH007100R0076
UPC Number: 78621058182
EAN Number: 05415022058000
Status: Active

Copper One-Hole Lug, Standard Barrel, Peep Hole, Max 35kV, Wire Size 535 kcmil, 5/8 Inch Bolt Size, Tin Plated, Die Code 99, Die Color Code Pink

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel
Standard	UL E9809
Cable Size	535 kcmil
Stud Size	5/8 Inch
Number Of Holes	1
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Pink

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Outer Quantity	20
Outer Dimensions (inches)	7.6x6.6x3.5
Weight Uom	61 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Instruction Sheet	TA00884-TB2

For further technical assistance, please contact us...

Thomas & Betts Canada
 700, Thomas Avenue
 Saint-Jean-sur-Richelieu, QC
 J2X 2M9
www.tnb.ca

T&B Technical Support
<http://www.tnb.ca/en/contactus/?id=ALL>

Hours: 7h00 - 18h00
 Monday-Friday