


CO22-U Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with compartment with or without breaker

Product specifications

- Conductor range: line: single ½ in. stud to accommodate compression lugs (supplied by utility), load: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for load sides
- For underground service only
- Factory pre-bussed from main lugs to each position
- Internal locking system for covers
- Supplied with screw type sealing rings
- Factory-installed 2 pole circuit breaker, 10,000 A rms interrupting capacity
- ABB type a2A (10 kA) or a2N (22kA) breaker
- With adjustable breaker plate for field installation of Square D type QBL, Eaton type ED breakers, Siemens type QJ,QJR,QR, QRH & SQD type QB
- CO3009A-KIT (ABB), CO3009-KIT (Siemens), CO3009SD-KIT (Square D) and CO3409FB-KIT (Eaton) conductor kits available (breakers not included) see page 64
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



Cat. no.	Type	Description	Position	Dimensions (in.)			Weight each	
				H	W	D	lb	kg
Left-hand entry								
CO22-U	Underground only	2 gang provision for ABB, Siemens, Eaton , SQD 10 kA rated breaker	2	30	26¼	5½	60	27.21
CO22-200-U	Underground only	Comes with 2 x ABB a2A type 10 kA rated breaker	2	30	26¼	5½	60	27.21
CO22-200HI-U	Underground only	Comes with 2 x ABB a2N type 22 kA rated breaker	2	30	26¼	5½	60	27.21
CO23-U	Underground only	3 gang provision for ABB, Siemens, Eaton , SQD 10 kA rated breaker	3	30	35	5½	80	36.29
CO23-200-U	Underground only	Comes with 3 x ABB a2A type 10 kA rated breaker	3	30	35	5½	80	36.29
CO23-200HI-U	Underground only	Comes with 3 x ABB a2N type 22 kA rated breaker	3	30	35	5½	80	36.29
CO24-U	Underground only	4 gang provision for ABB, Siemens, Eaton , SQD 10 kA, rated breaker	4	30	43¾	5½	100	45.36
CO24-200-U	Underground only	4 gang provision for ABB type a2a. Siemens, Eaton , SQD 10 kA rated breaker	4	30	43¾	5½	100	45.36
CO24-200HI-U	Underground only	Comes with 4 x ABB a2N type 22 kA rated breaker	4	30	43¾	5½	100	45.36

Note: Ex. CO22-XXX, suffix (XXX) can be replaced by any of the following breaker amperage options: 100, 125 or 150. Consult your regional sales office for price and availability. Consult your regional sales office for right-hand entry option.

CO22-U Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with compartment with or without breaker

Diagrams

