



**Splice Connector**  
**T&B Catalog Number:**

54505

**UPC Number:**

78621054505

**Status:**

Active

**Description:**

Copper Two-Way Splice - Short Barrel for 6 AWG, 61/24, 6 Weld, Die Code 24 Blue

**Features**

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

**General**

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#6 AWG
Wire Size Flex	61/24 = 24.6 kcmil, #6 Weld, 133/.014
Die Color	Blue
Die Code	24

**Dimension Information**

A (inches)	1.00
E (inches)	.30

**Specifications**

Voltage Rating	600V
----------------	------

**Packaging**

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	1.14 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:

Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com