

2522

T&B Industrial Fitting

Liquidtight strain relief fitting with a hub size of 1/2 in.



General

Type:	Flexible Cord and Cable Fittings
T&B UPC:	78621002522
T&B Status:	M
Special Features:	UL Listed as liquidtight strain relief, and outlet bushing. CSA certified watertight when used with 5262 Series Sealing Ring
Temperature Rating:	105 °C
Material:	Die Cast Zinc

Dimension Information

Hub Size (in.):	1/2
Throat Dia. (in.):	9/16
Dimension A (in.):	1-5/32
Dimension B (in.):	1-11/16
Dimension C (in.):	5/8
Cable Size (min.-max.):	0.375-0.500