

10605



## **T&B Industrial Fitting**

90 degrees watertight fittings made of malleable iron with a protective grounding sleeve for jacketed metal-clad cable. Hub thread size 3/4 in.

### General

T&B Instruction Sheets:	TA00316-TB2
Type:	90 degrees Watertight Fittings and Non-Watertight Teck Cable Fittings
Application:	Ordinary wet location
T&B UPC:	78621010605
T&B Status:	M
Hub Size:	3/4 in.
Material:	Malleable iron

### Dimension Information

Neoprene Bushing Max.:	1.205 in.
Neoprene Bushing Min.:	1.055 in.